

EHS High Precision HV Modules 16 Cannels with Common Floating-GND

Operator's Manual



Contents

- 1. General information
- 2. Technical data
- 3. Handling
- 3.1 Connection
- 3.2 Limits
- 3.3 Safety Loop
- 3.4 Option: Single Channel INHIBIT
- 4. Pin assignment and connector layout
- 5. Order Information



Attention!

- -It is not allowed to use the unit if the covers have been removed.
- -We decline all responsibility for damages and injuries caused by an improper use of the module. It is highly recommended to read the manual before any kind of operation.

Note

The information in this manual is subject to change without notice. We take no responsibility for any error in the document. We reserve the right to make changes in the product without notification to the users.

Filename EHSF2x-CFG as of 2011-06-10



1. General information

The EHS modules of this series are High Precision multichannel high voltage power supplies in 6U Eurocard format. The output voltage features an exceptionally high stability, lowest ripple and a very small temperature coefficient. The extreme small ripple is ensured down to very low frequencies (below 0.1Hz). Each single channel has an independent voltage and current control. The current measurement includes two measurement ranges with a resolution down to a few picoampere. The data for set and measure values is given in a format of Floating Point Single Precision values. The modules are equipped with 24 bit ADC and 20 bit DAC circuits. The channels share a Common Floating-GND (C-RTN), which avoids ground loops and reduces the noise level

The channels share a Common Floating-GND (C-RTN), which avoids ground loops and reduces the noise level in large systems. The Common Floating-GND is insulated from the Crate-Ground (CCG) up to ±50 V (with a 60 V hardware limit).

The HV output is available as a 51 pin REDEL HV connector or as isolated built-in BNC resp. SHV connectors.

This manual covers modules with 16 channels. These modules are also available with 8 channels (up to 8 kV) and 4 channels (10 KV) (see manual "EHS High Precision HV Modules 8 Channels with Common Floating-GND")

2. Technical data

| | EHS F201x) ¹ | EHS F205x) ¹ | EHS F210x) ¹ | EHS F220x) ¹ | EHS F230x) ¹ | EHS F240x) ¹ | EHS F260x) ¹ | |
|---|---|-------------------------|-------------------------|-------------------------|-------------------------|-------------------------|-------------------------|--|
| HV channels per module | 16 | 16 | 16 | 16 | 16 | 16 | 16 | |
| Output voltage V _{O nom} [kV] | 0.1 | 0.5 | 1 | 2 | 3 | 4 | 6 | |
| Output current I _{O nom} [mA] | 10 | 10 | 8 | 4 | 3 | 2 | 1 | |
| Resolution of voltage setting*) [mV] | 0.5 | 1 | 2 | 5 | 10 | 10 | 12 | |
| current setting*) [nA] | 30 | 30 | 20 | 10 | 5 | 4 | 2 | |
| voltage measurement*) [mV] | 0.5 | 1 | 2 | 5 | 10 | 10 | 12 | |
| current measurement* ⁾ [nA] 1 st measurement range I _{O nom} ≥ I _O ≥ 20 µA | 8 | 8 | 5 | 4 | 3 | 2 | 1 | |
| current measurement*) [pA] 2^{nd} measurement range $20\mu A \ge I_0 > 0$ | 50 | 50 | 50 | 50 | 50 | 50 | 50 | |
| Ripple and noise [mV _{P-P}] | < 3 < 5 < 20 | | | | | | | |
| | - at max. load and $ V_O $ > 1% * $V_{O nom}$ - f > 0.1 Hz | | | | | | | |
| Stability (no load/load and ΔV_{IN}) | < 0.01%* V _{O nom} | | | | | | | |
| Sample rates [samples/s] | 5, 10, 25, 50, 60, 100, 500 | | | | | | | |
| Digital filter averages | 1, 16, 64, 256, 512, 1024 | | | | | | | |
| The resolution of measurable values depends on the settings of the sampling rate and the digital filter! | | | | | | | | |
| Accuracy of voltage measurement | ± (0.01% * V _O + 0.02% * V _{O nom}) | | | | | | | |
| Accuracy of current measurement | 1^{st} measurement range $\pm (0.01\% * I_O + 0.02\% * I_{O nom})$ 2^{nd} measurement range $\pm (0.01\% * I_O + 4 nA)$ | | | | | | | |
| The measurement accuracy is guaranteed in the range 1% * $V_{O \text{ nom}}$ < $V_{O \text{ nom}}$ and for 1 year | | | | | | | | |
| Voltage ramp up / down [V/s] | 1*10 ⁻⁶ * V _{O nom} up to 0.2 * V _{O nom} | | | | | | | |
| Floating voltage | Common-GND to System-GND: ≤ 50 V | | | | | | | |
| *) with standard sample rate 50/s and digital filter 64 | | | | | | | | |

^{*)} with standard sample rate 50/s and digital filter 64



| | EHS F201x) ¹ | FHS F205x)1 | | EHS F210x) ¹ | EHS F220x) ¹ | EHS F230x)1 | , , , , , , , , , , , , , , , , , , , | EHS F240x'' | EHS F260x) ¹ |
|---|--|-------------|----|-------------------------|-------------------------|----------------------|---------------------------------------|-------------|-------------------------|
| Temperature coefficient | < ± 50 * 10 ⁻⁶ / _K | | | | | | | | |
| Hardware limits V _{max} / I _{max} | potentiometer per module (V _{max} / I _{max} is the same for all channels) | | | | | | | | |
| Interface | CAN-Interface (potential free) | | | | | | | | |
| Operating mode | Full module and channel control via CAN interface in EHS mode: EDCP (Enhanced Device Control Protocol) or EHQ mode: DCP (Device Control Protocol) see manual "CAN-Interface Operator's Manual" | | | | | | | | |
| Module status | green LED turns on if all channels have the status "ready" | | | | | | | | |
| Protection loop (I _s) potential free (2 pin Lemo-socket and REDEL SL) | ! | 5 mA < | | | | module c module c | | | |
| Option ID/IU: INHIBIT per channel | Via Sub-D-9 connector INHIBIT (TTL level) | | | | | | | | |
| INHIBIT 0-7 / Channel | 0 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | GND |
| 1 ^{st.} Sub-D-9 connector / PIN | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 |
| INHIBIT 8-15 / Channel | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | GND |
| 2 ^{nd.} Sub-D-9 connector / PIN | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 |
| Power requirements V _{INPUT} | + 24 V (< 8 A) and + 5 V (< 0.3 A) | | | | | | | | |
| Packing | 6U Euro cassette (40.64 mm wide and 220 mm deep) | | | | | | | | |
| Connector on the rear | 96-pin connector according to DIN 41612 | | | | | | | | |
| HV connector | 51 pin REDEL HV connector (R51) isolated built-in BNC connector (BNC) up to 100 V isolated built-in SHV connector (SHV) 500 V up to 6 kV | | | | | | | | |
| Operating temperature | 0 +40 °C | | | | | | | | |
| Storage temperature | -20 +6 | 30 °C | | | | | | | |

 $^{^{-)1}}x = p$: polarity positive, $^{)1}x = n$: polarity negative

3. Handling

3.1 Connection

The supply voltages and the CAN interface are connected to the module via a 96-pin connector on the rear side of the module.

The module is controlled in the selected CAN operating mode (EHS or EHQ), the factory setting is "EHS mode".

3.2 Limits

The maximum output voltage for all channels (hardware voltage limit) is defined through the position of the corresponding potentiometer V_{max} .

The maximum output current for all channels (hardware current limit) is defined through the position of the corresponding potentiometer I_{max} .

The greatest possible set value for voltage and current is given by $V_{max} - 2\%$ and $I_{max} - 2\%$, respectively.

It is possible to measure the hardware voltage and current limits at the sockets below the potentiometer. The socket voltages are proportional to the relative limits, where 2.5 V corresponds to 102 \pm 2 % $V_{O\ nom}$ and 102 \pm 2 % $I_{O\ nom}$.

The output voltage and current are limited to the specified value. If a limit is reached or exceeded in any channel the green LED on the front panel turns off.



3.3 Safety Loop

A safety loop can be implemented via the safety loop socket (SL) on the front panel and between the SLcontacts (Pin 22 and PIN 30) at the REDEL-connector if equipped. If the safety loop is active then an output voltage in any channel is only present if the safety loop is closed and an external current in a range of 5 to 20 mA of any polarity is driven through the loop. (For modules with a REDEL-connector the other SL input must be closed.) If the safety loop is opened during the operation the output voltages are shut off without ramp and the corresponding bits in the 'ModuleStatus' (see manual "CAN-Interface Operator's Manual" 5.5.2.1 ModuleStatus) and ModuleEventStatus (5.5.2.3 ModuleEventStatus) are cancelled. After closing the loop again the ModuleEventStatus has to be reset and the channels have to be switched ON.

The loop connectors are potential free, the internal voltage drop is approx. 3 V. In the factory setup the safety loop is not active (the corresponding bits are always set). The loop can be activated by removing the internal jumper. (see manual "CAN-Interface Operator's Manual", app. B).

Option: Single Channel INHIBIT

Optionally it is possible to install an INHIBIT for each channel via two Sub-D connectors. Channel 0 to 7 corresponds to Pin 1 to 8 at the 1st Sub-D connector, Pin 9 is connected to GND. Channel 8 to 15 corresponds to Pin 1 to 8 at the 2nd Sub-D connector, Pin 9 is connected to GND.

INHIBIT Option ID:

The INHIBIT pins are internally connected to the module GND with help of pull down resistors (approx. 10 k Ω). This ensures that a disconnected cable always causes an interlock. HV generation according to the settings is only possible with TTL High level on the INHIBIT pins!

INHIBIT Option _IU:

The INHIBIT pins are internally connected to 5V with help of pull up resistors (approx. 10 k Ω). HV generation according to the settings is possible with TTL High level or not connected INHIBIT pins.

If the INHIBIT contact pin (n) is connected to the CF-GND or a TTL-LOW potential the behavior of HV-PS in this channel depends on the following setting (5.5.2.2 ModuleControl, bit setKILena):

KILL-enable = 1: Voltage is switched off permanently without ramp. ChannelEventStatus flag 'EEINH' is set. The green LED at the front panel turns off.

KILL-enable = 0: ChannelStatus flag 'isEINH' and ChannelEventStatus flag EEINH are set. The action of the HV channel can be defined via the Monitoring group (5.5.3.3 Monitoring group, MonitorIsExternalInhibit). The green LED at the front panel turns off.

The INHIBIT active time (LOW potential) must be at least 100 ms!

When the INHIBIT is no longer active (TTL-HIGH potential or not connected), the INHIBIT flag must be reset before the voltage can be switched ON again (5.5.1.3 Channel event status).

4. Pin assignment and connector layout

Pin assignment of the 96-pin connector according to DIN 41612:


| pin | | pin | | pin | | comment |
|-----|----------|-----|------------|-----|--------|--|
| a1 | +5V | b1 | +5V | c1 | +5V | |
| a2 | GND | b2 | GND | c2 | GND | power supply |
| a3 | +24V | b3 | +24V | сЗ | +24V | power supply |
| a5 | GND | b5 | GND | c5 | GND | |
| a11 | @CAN_GND | b11 | @CAN_L | c11 | @CAN_H | CAN bus interface, potential free |
| a13 | /RESET | b13 | /HW_RMPDWN | | | external control signals |
| a30 | A4 | b30 | A5 | | | address field: |
| a31 | A2 | b31 | A3 | c31 | GND | set module address (A0 A5); pin connected to GND => address bit = 0 |
| a32 | A0 | b32 | A1 | c32 | | pin open => address bit = 1 |

/RESET active low; global reset of the module; HV generation is stopped immediately high - low - high with a puls-width from 1µs to 100 µs /HW_RMPDWN pulse form:

> function: ramp down all channels immediately with a ramp speed of V_{nom}/50s

Note: after activating this signal the ramp speed is set to V_{nom}/50s





CCG is connected with the Crate-GND and the shield

5. Order Information

| Item Code | Туре | Polarity | Channels | V_{nom} | I _{nom} | HV Connector |
|-----------------|-----------|----------|----------|-----------|------------------|--------------|
| EH162-60p105R51 | EHS F260p | positive | 16 | 6000V | 1mA | REDEL)1 |
| EH162-60n105R51 | EHS F260n | negative | 16 | 6000V | 1mA | REDEL)1 |
| EH162-40p205R51 | EHS F240p | positive | 16 | 4000V | 2mA | REDEL)1 |
| EH162-40n205R51 | EHS F240n | negative | 16 | 4000V | 2mA | REDEL)1 |
| EH162-30p305R51 | EHS F230p | positive | 16 | 3000V | 3mA | REDEL)1 |
| EH162-30n305R51 | EHS F230n | negative | 16 | 3000V | 3mA | REDEL)1 |
| EH162-20p405R51 | EHS F220p | positive | 16 | 2000V | 4mA | REDEL)1 |
| EH162-20n405R51 | EHS F220n | negative | 16 | 2000V | 4mA | REDEL)1 |
| EH162-10p805R51 | EHS F210p | positive | 16 | 1000V | 8mA | REDEL)1 |
| EH162-10n805R51 | EHS F210n | negative | 16 | 1000V | 8mA | REDEL)1 |
| EH162-05p106R51 | EHS F205p | positive | 16 | 500V | 10mA | REDEL)1 |
| EH162-05n106R51 | EHS F205n | negative | 16 | 500V | 10mA | REDEL)1 |
| EH162-01p106R51 | EHS F201p | positive | 16 | 100V | 10mA | REDEL)1 |
| EH162-01n106R51 | EHS F201n | negative | 16 | 100V | 10mA | REDEL)1 |

⁾¹ Option SHV instead of R51 => Connector SHV

⁾² Option BNC instead of R51 => Connector BNC