

EHS Standard HV Modules 16 Channels with Single Channel Floating-GND

Operator's Manual



Contents

- 1. General information
- 2. Technical data
- 3. Handling
- 3.1 Connection
- 3.2 Limits
- 3.3 Safety Loop
- 3.4 Option: Single Channel INHIBIT
- 4. Pin assignment and connector layout
- 5. Order Information

Crates with Power Supplies

CAN-Interface Operator's Manual



Attention!

- -It is not allowed to use the unit if the covers have been removed.
- -We decline all responsibility for damages and injuries caused by an improper use of the module. It is highly recommended to read the manual before any kind of operation.

Note

The information in this manual is subject to change without notice. We take no responsibility for any error in the document. We reserve the right to make changes in the product design without notification to the users.

Filename EHSF6x-F as of 2011-06-10



1. General information

The EHS modules of this series are Standard multichannel high voltage power supplies in 6U Eurocard format. The output voltage features a high stability, low ripple and noise and low temperature coefficient. Each single channel has an independent voltage and current control. The data for set and measure values is given in a format of Floating Point Single Precision values. The modules are equipped with 24 bit ADC and 20 bit DAC circuits.

The outputs RTN - floating HV-GND - of each channel are floating against each other and against ground (with a 25 V hardware limit). Optional the floating voltage can be increased to up to 2 kV.

The HV output is available as a 51 pin REDEL HV connector or as isolated built-in SHV connectors.

This manual covers modules with 16 channels. These modules are also available with 8 channels (up to 8 kV) and 4 channels (10 KV) (see manual "EHS Standard HV Modules 8 Channels with Single Channel Floating-GND")

2. Technical data

	EHS F601x-F)1	EHS F605x-F)1	EHS F610x-F) ¹	EHS F620x-F) ¹	EHS F630x-F)1	EHS F640x-F)1	EHS F660x-F)1	
HV channels per module	16	16	16	16	16	16	16	
Output voltage V _{O nom} [kV]	0.1	0.5	1	2	3	4	6	
Output current Io nom [mA]	10	15	8	4	3	2	1	
Resolution of voltage setting*) [mV]	5	20	40	80	120	160	240	
current setting ^{*)} [nA]	400	600	320	160	120	80	40	
voltage measurement ^{*)} [mV]	1	2	4	5	10	10	15	
current measurement*) [nA]	100	150	80	40	30	20	10	
Ripple and noise [mV _{P-P}]	< 5 < 10 < 30 - at max. load and $ V_0 > 2\% * V_{0 \text{ nom}}$ - f > 10 Hz					< 30		
Stability(no load/load and Δ V _{IN})	0.02%* V _{O nom}							
Sample rates [samples/s]	5, 10, 25, 50, 60, 100, 500							
Digital filter averages	1, 16, 64, 256, 512, 1024							
The resolution of measurable values depends on the settings of the sampling rate and the digital filter!							er!	
Accuracy of voltage measurement $\pm (0.01\% * V_O + 0.02\% * V_{O nom})$								
Accuracy of current measurement								
The measurement accuracy is guaranteed in the range 2% * $V_{O \text{ nom}} < V_{O} \le V_{O \text{ nom}}$ and for 1 year								
Voltage ramp up / down [V/s]	1*10	1*10 ⁻⁶ * V _{O nom} up to 0.2 * V _{O nom}						
Floating voltage	Connector RTN to GND: ≤ 20 V							
Temperature coefficient	$< \pm 50 * 10^{-6}/_{K}$							
Hardware limits V_{max} / I_{max} potentiometer per module $(V_{max} / I_{max}$ is the same for all channels)						nels)		
*) with standard sample rate 500/s and digital filter 64								

^{*)} with standard sample rate 500/s and digital filter 64



EHS F601x-F)1	EHS F605x-F)1		EHS F610x-F)1	EHS F620x-F)1	EHS F630x-F)1		EHS F640X-F7	EHS F660x-F ⁾¹
CAN-Interface (potential free)								
Operating mode Full module and channel control via CAN interface in EHS mode: EDCP (Enhanced Device Control Protocol or EHQ mode: DCP (Device Control Protocol) see manual "CAN-Interface Operator's Manual"						otocol)		
green LED turns on if all channels have the status "ready"								
5	$5 \text{ mA} < I_s < 20 \text{ mA} \qquad \Rightarrow \qquad \text{module on} \\ I_s < 0.5 \text{ mA} \qquad \Rightarrow \qquad \text{module off}$							
Via Sub-D-9 connector INHIBIT (TTL level)								
0	1	2	3	4	5	6	7	GND
1	2	3	4	5	6	7	8	9
8	9	10	11	12	13	14	15	GND
1	2	3	4	5	6	7	8	9
+ 24 V (< 8,5 A) and + 5 V (< 0.3 A)								
6U Euro cassette (40.64 mm wide and 220 mm deep)								
96-pin connector according to DIN 41612								
51 pin REDEL HV connector (R51) or isolated built-in SHV connector (SHV)								
0 +40 °C								
-20 +60 °C								
,	CAN-Inte Full modu or s green LE Via Sub-I 0 1 8 1 + 24 V (6U E 96-pin 51 pin isolate 0	CAN-Interface (por EHS modor EHQ modor EHQ modor See manus) The see manus of the see manus	CAN-Interface (potential Full module and channe EHS mode: or EHQ mode: see manual "Control of the see manual" of the see manual "Control of the see manual" of the see manual "Control of the see manual" of the see manual "Control of the s	CAN-Interface (potential free) Full module and channel contresh EHS mode: EDCP or EHQ mode: DCP see manual "CAN-Interface of the control of t	CAN-Interface (potential free) Full module and channel control via CAN-EHS mode: EDCP (Enhance of EHQ mode: DCP (Device see manual "CAN-Interface Opergreen LED turns on if all channels have of the see manual "CAN-Interface Opergreen LED turns on if all channels have of the see manual "CAN-Interface Opergreen LED turns on if all channels have of the see manual "CAN-Interface Opergreen LED turns on if all channels have of the see manual "CAN-Interface Opergreen LED turns on if all channels have of the see manual "CAN-Interface Opergreen LED turns on if all channels have of the see manual "CAN-Interface Opergreen LED turns on if all channels have of the see manual "CAN-Interface Opergreen LED turns on if all channels have of the see manual "CAN-Interface Opergreen LED turns on if all channels have of the see manual "CAN-Interface Opergreen LED turns on if all channels have of the see manual "CAN-Interface Opergreen LED turns on if all channels have of the see manual "CAN-Interface Opergreen LED turns on if all channels have of the see manual "CAN-Interface Opergreen LED turns on if all channels have of the see manual "CAN-Interface Opergreen LED turns on if all channels have on the see manual "CAN-Interface Opergreen LED turns on if all channels have on the see manual "CAN-Interface Opergreen LED turns on if all channels have on the see manual "CAN-Interface Opergreen LED turns on if all channels have on the see manual "CAN-Interface Opergreen LED turns on if all channels have on the see manual "CAN-Interface Opergreen LED turns on if all channels have on the see manual "CAN-Interface Opergreen LED turns on if all channels have on the see manual "CAN-Interface Opergreen LED turns on if all channels have on the see manual "CAN-Interface Opergreen LED turns on if all channels have on the see manual "CAN-Interface Opergreen LED turns on if all channels have on the see manual "CAN-Interface Opergreen LED turns on if all channels have on the see manual "CAN-Interface Opergreen LED turns on if all channels have on the	CAN-Interface (potential free) Full module and channel control via CAN interface EHS mode: EDCP (Enhanced Device Or EHQ mode: DCP (Device Control P see manual "CAN-Interface Operator's Magreen LED turns on if all channels have the status 5 mA < I _s < 20 mA	CAN-Interface (potential free) Full module and channel control via CAN interface in EHS mode: EDCP (Enhanced Device Conor EHQ mode: DCP (Device Control Protocosee manual "CAN-Interface Operator's Manual" green LED turns on if all channels have the status "read 5 mA < I _s < 20 mA Society module on module off wia Sub-D-9 connector INHIBIT (TTL level) O	CAN-Interface (potential free) Full module and channel control via CAN interface in EHS mode: EDCP (Enhanced Device Control Proof or EHQ mode: DCP (Device Control Protocol) see manual "CAN-Interface Operator's Manual" green LED turns on if all channels have the status "ready" 5 mA < I _s < 20 mA

 $^{^{11}}x = p$: polarity positive, $^{11}x = n$: polarity negative

3. Handling

3.1 Connection

The supply voltages and the CAN interface are connected to the module via a 96-pin connector on the rear side of the module.

The module is controlled in the selected CAN operating mode (EHS or EHQ), the factory setting is "EHS mode".

3.2 Limits

The maximum output voltage for all channels (hardware voltage limit) is defined through the position of the corresponding potentiometer V_{max} .

The maximum output current for all channels (hardware voltage limit) is defined through the position of the corresponding potentiometer I_{max} .

The greatest possible set value for voltage and current is given by $V_{max} - 2\%$ and $I_{max} - 2\%$, respectively.

It is possible to measure the hardware voltage and current limits at the sockets below the potentiometer. The socket voltages are proportional to the relative limits, where 2.5 V corresponds to 102 \pm 2 % $V_{O\ nom}$ and 102 \pm 2 % $I_{O\ nom}$.

The output voltage and current are limited to the specified value. If a limit is reached or exceeded in any channel the green LED on the front panel turns off.



3.3 Safety Loop

A safety loop can be implemented via the safety loop socket (SL) on the front panel and between the SL-contacts (Pin 22 and PIN 30) at the REDEL-connector if equipped. If the safety loop is active then an output voltage in any channel is only present if the safety loop is closed and an external current in a range of 5 to 20 mA of any polarity is driven through the loop. (For modules with a REDEL-connector the other SL input must be closed.) If the safety loop is opened during the operation the output voltages are shut off without ramp and the corresponding bits in the 'ModuleStatus' (see manual "CAN-Interface Operator's Manual" 5.5.2.1 ModuleStatus) and ModuleEventStatus (5.5.2.3 ModuleEventStatus) are cancelled. After closing the loop again the ModuleEventStatus has to be reset and the channels have to be switched ON.

The loop connectors are potential free, the internal voltage drop is approx. 3 V. In the factory setup the safety loop is not active (the corresponding bits are always set). The loop can be activated by removing the internal jumper. (see manual "CAN-Interface Operator's Manual", app. B).

3.4 Option: Single Channel INHIBIT

Optionally it is possible to install an INHIBIT for each channel via two Sub-D connectors. Channel 0 to 7 corresponds to Pin 1 to 8 at the 1st Sub-D connector, Pin 9 is connected to GND. Channel 8 to 15 corresponds to Pin 1 to 8 at the 2nd Sub-D connector, Pin 9 is connected to GND.

INHIBIT Option _ID:

The INHIBIT pins are internally connected to the module GND with help of pull down resistors (approx. 10 k Ω). This ensures that a disconnected cable always causes an interlock. HV generation according to the settings is only possible with TTL High level on the INHIBIT pins!

INHIBIT Option IU:

The INHIBIT pins are internally connected to 5V with help of pull up resistors (approx. 10 k Ω). HV generation according to the settings is possible with TTL High level or not connected INHIBIT pins.

If the INHIBIT contact pin (n) is connected to the CF-GND or a TTL-LOW potential the behavior of HV-PS in this channel depends on the following setting (5.5.2.2 ModuleControl, bit setKILena):

KILL-enable = 1: Voltage is switched off permanently without ramp. ChannelEventStatus flag 'EEINH' is set.

The green LED at the front panel turns off.

KILL-enable = 0: ChannelStatus flag 'isEINH' and ChannelEventStatus flag EEINH are set. The action of the HV channel can be defined via the Monitoring group (5.5.3.3 Monitoring group, MonitorIsExternalInhibit). The green LED at the front panel turns off.

The INHIBIT active time (LOW potential) must be at least 100 ms!

When the INHIBIT is no longer active (TTL-HIGH potential or not connected), the INHIBIT flag must be reset before the voltage can be switched ON again (5.5.1.3 Channel event status).

4. Pin assignment and connector layout

Pin assignment of the 96-pin connector according to DIN 41612:

pin		pin		pin		comment
a1	+5V	b1	+5V	c1	+5V	
a2	GND	b2	GND	c2	GND	power supply
а3	+24V	b3	+24V	c3	+24V	power supply
а5	GND	b5	GND	c5	GND	
a11	@CAN_GND	b11	@CAN_L	c11	@CAN_H	CAN bus interface, potential free
a13	/RESET	b13	/HW_RMPDWN			external control signals
a30	A4	b30	A5			address field:
a31	A2	b31	А3	c31	(÷IXII)	set module address (A0 A5); pin connected to GND => address bit = 0
a32	A0	b32	A1	c32		pin open => address bit = 1


/RESET active low; global reset of the module; HV generation is stopped immediately /HW_RMPDWN pulse form: high – low – high with a puls-width from 1µs to 100 µs

function: ramp down all channels immediately with a ramp speed of V_{nom} /50s

Note: after activating this signal the ramp speed is set to V_{nom}/50s



51 pin REDEL HV connector



5. Order Information

Item Code	Туре	Polarity	Channels	V_{nom}	I _{nom}	HV Connector
EH166-66p105FR51	EHS F660p-F	positive	16	6000V	1mA	REDEL ⁾¹
EH166-66n105FR51	EHS F660n-F	negative	16	6000V	1mA	REDEL ⁾¹
EH166-40p205FR51	EHS F640p-F	positive	16	4000V	2mA	REDEL ⁾¹
EH166-40n205FR51	EHS F640n-F	negative	16	4000V	2mA	REDEL ⁾¹
EH166-30p305FR51	EHS F630p-F	positive	16	3000V	3mA	REDEL ⁾¹
EH166-30n305FR51	EHS F630n-F	negative	16	3000V	3mA	REDEL ⁾¹
EH166-20p405FR51	EHS F620p-F	positive	16	2000V	4mA	REDEL ⁾¹
EH166-20n405FR51	EHS F620n-F	negative	16	2000V	4mA	REDEL ⁾¹
EH166-10p805FR51	EHS F610p-F	positive	16	1000V	8mA	REDEL ⁾¹
EH166-10n805FR51	EHS F610n-F	negative	16	1000V	8mA	REDEL ⁾¹
EH166-05p156FR51	EHS F605p-F	positive	16	500V	15mA	REDEL ⁾¹
EH166-05n156FR51	EHS F605n-F	negative	16	500V	15mA	REDEL ⁾¹
EH166-01p106FR51	EHS F601p-F	positive	16	100V	10mA	REDEL ⁾¹
EH166-01n106FR51	EHS F601n-F	negative	16	100V	10mA	REDEL ⁾¹

)1 Option SHV instead of R51 => Connector SHV